

Classic filament LEDbulbs

CLA LEDBulb ND 4-40W ST64 E27 827 CL

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4-40W

Light Technical	
Colour code	827 [CCT of 2,700 K]
Luminous flux (nom.)	470 lm
Luminous flux (rated) (nom.)	470 lm
Colour designation	Warm White (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	118.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	33 mA
Wattage equivalent	40 W

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	4 kWh


Product Data	
Full product code	871869657403400
Order product name	CLA LEDBulb ND 4-40W ST64 E27 827 CL
EAN/UPC – product	8718696574034
Order code	57403400

Classic filament LEDbulbs

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001237302

Net weight (piece)	0.030 kg
--------------------	----------



Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
CLA LEDBulb ND 4-40W ST64 E27 827 CL	64 mm	140 mm

Photometric data



CorePro LEDbulb ND 4-40W ST64 827



Classic filament LEDbulbs

