

Classic filament LEDbulbs

CLA LEDBulb ND 4-40W ST64 E27 827 CL

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E27 [E27] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 20,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 827 [CCT of 2700K] |
| Luminous Flux | 470 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 118.00 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 4 W |
| Lamp Current (Nom) | 33 mA |

| Wattage Equivalent | 40 W |
|-------------------------------|-----------|
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.4 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case Maximum (Nom) | 70 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | ST64 |
| Approval and Application | |
| Energy Saving Product | Yes |
| Suitable For Accent Lighting | No |
| Energy Consumption kWh/1000 h | 4 kWh |
| EyeComfort | Yes |

Classic filament LEDbulbs

| Product Data | |
|---------------------|--------------------------------------|
| Order product name | CLA LEDBulb ND 4-40W ST64 E27 827 CL |
| Full product name | CLA LEDBulb ND 4-40W ST64 E27 827 CL |
| Full product code | 871869657403400 |
| Order code | 57403400 |
| Material Nr. (12NC) | 929001237302 |


Dimensional drawing




| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696574034 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718696574041 |

| Product | D | C |
|--------------------------------------|-------|--------|
| CLA LEDBulb ND 4-40W ST64 E27 827 CL | 64 mm | 140 mm |


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb ND 4-40W ST64 E27 827 CL




General uniform lighting - CLA LEDBulb ND 4-40W ST64 E27 827 CL




Light Distribution Diagram - CLA LEDBulb ND 4-40W ST64 E27 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 4-40W ST64 E27 827 CL



Lumen Maintenance Diagram - CLA LEDBulb ND 4-40W ST64 E27 827 CL

