



Classic filament LED candles and lusters



CLA LEDCandle ND 2-25W B35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data


General Information			
Cap-Base	E14 [E14]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	2 W
Switching Cycle	20,000	Lamp Current (Nom)	20 mA
Lighting Technology	LED	Wattage Equivalent	25 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	36 °C
Luminous Flux	250 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	125.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	B35 [B 35mm]
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic filament LED candles and lusters

Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	387351
EyeComfort	Yes
Product Data	
Order product name	CLA LEDCandle ND 2-25W B35 E14 827 CL


Full product name	CLA LEDCandle ND 2-25W B35 E14 827 CL
Full product code	871869657407200
Order code	929001238302
Material Nr. (12NC)	929001238302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574072
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574089

Dimensional drawing




Product	D	C
CLA LEDCandle ND 2-25W B35 E14 827 CL	35 mm	97 mm

Photometric data




Spectral Power Distribution Colour - CLA LEDCandle ND 2-25W B35 E14 827 CL



General uniform lighting - CLA LEDCandle ND 2-25W B35 E14 827 CL


Classic filament LED candles and lusters

Photometric data




Light Distribution Diagram - CLA LEDCandle ND 2-25W B35 E14 827 CL

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 2-25W B35 E14 827 CL



Lumen Maintenance Diagram - CLA LEDCandle ND 2-25W B35 E14 827 CL

