



Classic filament LEDbulbs

LEDClassic 2-25W B35 E14 WW CL ND APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	2-25W
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	250 lm
Lamp Luminous Flux (Nom)	250 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	125.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	2 W

Lamp current (nom.)	20 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	2 kWh


Classic filament LEDbulbs

Product Data

Full product code	871869657427000
Order product name	LEDClassic 2-25W B35 E14 WW CL ND APR
EAN/UPC – product	8718696574270
Order code	929001238308
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001238308
Net weight (piece)	0.014 kg


Dimensional drawing




filament 2.5W-25W 250lm NAD 2700K E14ND

Product	D	C
LEDClassic 2-25W B35 E14 WW CL ND APR	35 mm	97 mm


Photometric data



LED Lamps, Lightcolour /827 ND CL




Classic LEDCandle ND 2-25W B35 827 CL




Classic LEDCandle ND 2-25W B35 827 CL

Classic filament LEDbulbs

Lifetime



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND

