



Classic filament LED candles and lusters



Classic LEDCandle ND 2-25W BA35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	36 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	BA35

Classic filament LED candles and lusters

Approval and Application


Energy Efficiency Class	E
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	387361
EyeComfort	Yes

Product Data

Order product name	CLA LEDCandle ND 2-25W BA35 E14 827 CL
--------------------	--



Full product name	Classic LEDCandle ND 2-25W BA35 E14 827 CL
Full product code	871869657409600
Order code	57409600
Material Nr. (12NC)	929001238402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574096
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574102

Dimensional drawing



Product	D	C
CLA LEDCandle ND 2-25W BA35 E14 827 CL	35 mm	123 mm

Photometric data




Spectral Power Distribution Colour - CLA LEDCandle ND 2-25W BA35 E14 827 CL

General uniform lighting - CLA LEDCandle ND 2-25W BA35 E14 827 CL

Classic filament LED candles and lusters

Photometric data



Light Distribution Diagram - CLA LEDCandle ND 2-25W BA35 E14 827 CL

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 2-25W BA35 E14 827 CL



Lumen Maintenance Diagram - CLA LEDCandle ND 2-25W BA35 E14 827 CL

