



Classic filament LED candles and lusters

Classic LEDCandle ND 2-25W BA35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E14 [E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	2-25W
Flux measurement reference	Sphere

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Nom)	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	36 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	BA35

Approval and Application	
Energy Efficiency Class	E

Classic filament LED candles and lusters

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	387361
Product Data	
Full product code	871869657409600
Order product name	Classic LEDCandle ND 2-25W BA35 E14 827 CL

EAN/UPC - Product	8718696574096
Order code	929001238402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001238402
Net Weight (Piece)	0.014 kg



Dimensional drawing



Product	D	C
Classic LEDCandle ND 2-25W BA35 E14 827 CL	35 mm	123 mm


filament 2.5W-25W 250lm NAD 2700K E14ND

Photometric data



LED Lamps, Lightcolour /827 ND CL

Classic LEDCandle ND 2-25W BA35 827 CL




Classic LEDCandle ND 2-25W BA35 827 CL

Classic filament LED candles and lusters

Lifetime



15K LED



15K LMP

