



Classic filament LEDbulbs

LEDClassic 2-25W BA35 E14 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	BA35


Classic filament LEDbulbs

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh

Product Data	
Order product name	LEDClassic 2-25W BA35 E14 WW CL ND APR
Full product name	LEDClassic 2-25W BA35 E14 WW CL ND APR
Full product code	871869657429400


Order code	929001238408
Material Nr. (12NC)	929001238408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574294
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574300

Dimensional drawing




Product	D	C
LEDClassic 2-25W BA35 E14 WW CL ND APR	35 mm	123 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 2-25W BA35 E14 WW CL ND APR



General uniform lighting - LEDClassic 2-25W BA35 E14 WW CL ND APR



Light Distribution Diagram - LEDClassic 2-25W BA35 E14 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 2-25W BA35 E14 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 2-25W BA35 E14 WW CL ND APR

