



Classic filament LEDbulbs

LEDClassic 2-25W P45 E14 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

| General Information | |
|---------------------------------------|--------------------|
| Cap-Base | E14 [E14] |
| Nominal lifetime | 15000 hour(s) |
| Switching Cycle | 20000 |
| Rated Lifetime (Hours) | 15000 hour(s) |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 827 [CCT of 2700K] |
| Luminous Flux | 250 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 125.00 lm/W |
| Color Consistency | <lt/>6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |


| Input Frequency | 50 to 60 Hz |
|---------------------------|--------------|
| Power Consumption | 2 W |
| Lamp Current (Nom) | 20 mA |
| Wattage Equivalent | 25 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.4 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case Maximum (Nom) | 70 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | P45 [P 45mm] |

Classic filament LEDbulbs

| | |
|-------------------------------|---------------------------------------|
| Approval and Application | |
| Energy Consumption kWh/1000 h | 2 kWh |
| Product Data | |
| Order product name | LEDClassic 2-25W P45 E14 WW CL ND APR |
| Full product name | LEDClassic 2-25W P45 E14 WW CL ND APR |
| Full product code | 871869657431700 |
| Order code | 929001238608 |


| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 929001238608 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696574317 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718696574324 |

Dimensional drawing




| Product | D | C |
|---------------------------------------|-------|-------|
| LEDClassic 2-25W P45 E14 WW CL ND APR | 45 mm | 80 mm |


Photometric data



Spectral Power Distribution Colour - LEDClassic 2-25W P45 E14 WW CL ND APR



Light Distribution Diagram - LEDClassic 2-25W P45 E14 WW CL ND APR



General uniform lighting - LEDClassic 2-25W P45 E14 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 2-25W P45 E14 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 2-25W P45 E14 WW CL ND APR

