



# Classic filament LED Lamps

## LEDClassic 2-25W P45 E14 WW CL ND APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data


| General Information                    |                     | Lamp current (nom.)              |                                       |
|--|---------------------|----------------------------------|---------------------------------------|
| Cap base                               | E14 [ E14]          |                                  | 20 mA                                 |
| Nominal lifetime (nom.)                | 15000 h             | Wattage equivalent               | 25 W                                  |
| Switching cycle                        | 20000X              | Starting time (nom.)             | 0.5 s                                 |
| Technical type                         | 2-25W               | Warm-up time to 60% light (nom.) | 0.5 s                                 |
|  |                     | Power factor (nom.)              | 0.4                                   |
|  |                     | Voltage (nom.)                   | 220-240 V                             |
| Light Technical                        |                     | Controls and Dimming             |                                       |
| Colour Code                            | 827 [ CCT of 2700K] | Dimmable                         | No                                    |
| Lamp Luminous Flux 25°C EL (Nom)       | 250 lm              |                                  |                                       |
| Lamp Luminous Flux (Nom)               | 250 lm              | Mechanical and Housing           |                                       |
| Colour Designation                     | Warm white (WW)     | Bulb finish                      | Clear                                 |
| Colour Temperature, horizontal (Nom)   | 2700 K              |                                  |                                       |
| Lamp Luminous Efficacy EM (Nom)        | 125.00 lm/W         | Approval and Application         |                                       |
| Colour consistency                     | <6                  | Energy efficiency label (EEL)    | A++                                   |
| Colour Rendering Index,horiz (Nom)     | 80                  | Energy Consumption kWh/1000 h    | 2 kWh                                 |
| LLMF at end of nominal lifetime (nom.) | 70 %                |                                  |                                       |
| Operating and Electrical               |                     | Product Data                     |                                       |
| Input frequency                        | 50 to 60 Hz         | Full product code                | 871869657431700                       |
| Technical Lamp Power (Nom)             | 2 W                 | Order product name               | LEDClassic 2-25W P45 E14 WW CL ND APR |

# Classic filament LED Lamps

|                                 |               |
|---------------------------------|---------------|
| EAN/UPC – product               | 8718696574317 |
| Order code                      | 929001238608  |
| Numerator – quantity per pack   | 1             |
| Numerator – packs per outer box | 10            |

|                     |              |
|---------------------|--------------|
| Material no. (12NC) | 929001238608 |
| Net weight (piece)  | 0.014 kg     |




## Dimensional drawing



| Product                               | D     | C     |
|---------------------------------------|-------|-------|
| LEDClassic 2-25W P45 E14 WW CL ND APR | 45 mm | 80 mm |

filament 2.5W-25W 250lm NAD 2700K E14ND

## Photometric data



## Classic filament LED Lamps

