



Classic filament LEDbulbs

LEDClassic 2-25W P45 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	2-25W
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	250 lm
Lamp Luminous Flux (Nom)	250 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	125.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	2 W


Lamp current (nom.)	20 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A++
Energy Consumption kWh/1000 h	2 kWh
Product Data	
Full product code	871869657433100
Order product name	LEDClassic 2-25W P45 E27 WW CL ND APR

Classic filament LEDbulbs

EAN/UPC – product	8718696574331
Order code	929001238708
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001238708
Net weight (piece)	0.014 kg


Dimensional drawing




filament 2.5W-25W 250lm NAD 2700K E27ND

Product	D	C
LEDClassic 2-25W P45 E27 WW CL ND APR	45 mm	78 mm


Photometric data



LED Lamps, Lightcolour /827 ND CL



Classic LEDCandle ND 2-25W P45 827 CL



Classic LEDCandle ND 2-25W P45 827 CL

Classic filament LEDbulbs

