



Classic filament LEDbulbs

LEDClassic 2-25W P45 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	2 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	20 mA
Switching Cycle	20,000	Wattage Equivalent	25 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.4
Color Code	827 [CCT of 2700K]	Voltage (Nom)	220-240 V
Luminous Flux	250 lm	Temperature	
Color Designation	Warm White (WW)	T-Case Maximum (Nom)	70 °C
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	P45 [P 45mm]
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Approval and Application	
Energy Consumption kWh/1000 h	2 kWh
Product Data	
Order product name	LEDClassic 2-25W P45 E27 WW CL ND APR
Full product name	LEDClassic 2-25W P45 E27 WW CL ND APR
Full product code	871869657433100
Order code	929001238708


Material Nr. (12NC)	929001238708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574331
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574348

Dimensional drawing




Product	D	C
LEDClassic 2-25W P45 E27 WW CL ND APR	45 mm	78 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 2-25W P45 E27 WW CL ND APR



Light Distribution Diagram - LEDClassic 2-25W P45 E27 WW CL ND APR




General uniform lighting - LEDClassic 2-25W P45 E27 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 2-25W P45 E27 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 2-25W P45 E27 WW CL ND APR

