

Classic filament LEDbulbs

LEDClassic 6-70W G93 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Wattage Equivalent	
Cap-Base	E27 [E27]	70 W	
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	
Switching Cycle	20,000	0.5 s	
Lighting Technology	LED	Warm-up time to 60% light	
EU RoHS compliant	Yes	0.5 s	
Light Technical		Power Factor (Fraction)	
Color Code	827 [CCT of 2700K]	0.5	
Luminous Flux	806 lm	Voltage (Nom)	
Color Designation	Warm White (WW)	220-240 V	
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	134.00 lm/W	Dimmable	
Color Consistency	<6	No	
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	
Operating and Electrical		Clear	
Line Frequency	50 to 60 Hz	Bulb Shape	
Input Frequency	50 to 60 Hz	G93 [G 93mm]	
Power Consumption	6 W	Approval and Application	
Lamp Current (Nom)	52 mA	Energy Saving Product	
		Yes	
		Suitable For Accent Lighting	
		No	
		Energy Consumption kWh/1000 h	
		6 kWh	
		Product Data	
		Order product name	
		LEDClassic 6-70W G93 E27 WW CL ND APR	
		Full product name	
		LEDClassic 6-70W G93 E27 WW CL ND APR	
		Full product code	
		871869657435500	

Classic filament LEDbulbs

Order code	57435500
Material Nr. (12NC)	929001238808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574355


Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574362

Dimensional drawing




Product	D	C
LEDClassic 6-70W G93 E27 WW CL ND APR	95 mm	140 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 6-70W G93 E27 WW CL ND APR



General uniform lighting - LEDClassic 6-70W G93 E27 WW CL ND APR



Light Distribution Diagram - LEDClassic 6-70W G93 E27 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 6-70W G93 E27 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 6-70W G93 E27 WW CL ND APR

