



Classic filament LEDbulbs

LEDClassic 6-70W G93 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	6-70W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	806 lm
Luminous Flux (Rated) (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	6 W


Lamp Current (Nom)	52 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh
Product Data	
Full product code	871869657435500

Classic filament LEDbulbs

Order product name	LEDClassic 6-70W G93 E27 WW CL ND APR
EAN/UPC - Product	8718696574355
Order code	929001238808
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Material Nr. (12NC)	929001238808
Net Weight (Piece)	0.070 kg



Dimensional drawing




filament 7.5W-60W 806lm NAD 2700K E27ND

Product	D	C
LEDClassic 6-70W G93 E27 WW CL ND APR	95 mm	140 mm

Photometric data



Classic LEDGlobe ND 6-60W G93 E27 827 CL



Classic filament LEDbulbs

