



MASTER LEDspot PAR

MASLEDspot D 5.5-60W 827WW PAR38 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.


Product data

General Information		Power Consumption	
Cap-Base	E27 [E27]		5.5 W
Nominal lifetime	20,000 hour(s)	Lamp Current (Nom)	30 mA
Switching Cycle	50,000	Wattage Equivalent	60 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.85
Color Code	827 [CCT of 2700K]	Voltage (Nom)	220-240 V
Beam Angle (Nom)	25 degree(s)	Temperature	
Luminous Flux	550 lm	T-Case Maximum (Nom)	50 °C
Luminous Intensity (Nom)	2,300 cd	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	90.91 lm/W	Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	Energy Saving Product	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting	Yes
Luminous Flux in 90° Cone (Rated)	500 lm	Energy Consumption kWh/1000 h	6 kWh
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		


MASTER LEDspot PAR

Product Data	
Order product name	MASLEDspot D 5.5-60W 827WW PAR38 25D
Full product name	MASLEDspot D 5.5-60W 827WW PAR38 25D
Full product code	871869657829200
Order code	929001239302
Material Nr. (12NC)	929001239302

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - MASLEDspot D 5.5-60W 827WW PAR38 25D

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696578292
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696578308

Product	D	C
MASLEDspot D 5.5-60W 827WW PAR38 25D	124 mm	132 mm



General uniform lighting - MASLEDspot D 5.5-60W 827WW PAR38 25D



Light Distribution Diagram - MASLEDspot D 5.5-60W 827WW PAR38 25D

MASTER LEDspot PAR

