



CorePro LEDspot LV

CoreProLEDspotLV ND 4.7-35W 840 MR16 36D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	GU5.3 [GU5.3]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	840 [CCT of 4000K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	395 lm
Luminous intensity (nom.)	900 cd
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	84.04 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	395 lm
Operating and Electrical	
Power Consumption	4.7 W
Lamp current (nom.)	580 mA


Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.5
Voltage (nom.)	12 V
Temperature	
T-Case maximum (nom.)	76 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	MR16 [2 inch/50 mm]
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	6 kWh
Product Data	
Order product name	CoreProLEDspotLV ND 4.7-35W 840 MR16 36D
Full product name	CoreProLEDspotLV ND 4.7-35W 840 MR16 36D

CorePro LEDspot LV

Full EOC	871869657945900
Order code	57945900
Material no. (12 NC)	929001240402
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696579459



Numerator – packs per outer box	10
EAN/UPC – Case	8718696579466

Dimensional drawing




Product	D	C
CoreProLEDspotLV ND 4.7-35W 840 MR16 36D	50 mm	46 mm

Photometric data



Spectral Power Distribution Colour – CoreProLEDspotLV ND 4.7-35W 840 MR16 36D

General uniform lighting – CoreProLEDspotLV ND 4.7-35W 840 MR16 36D



Light Distribution Diagram – CoreProLEDspotLV ND 4.7-35W 840 MR16 36D

