



# MASTER LEDspot ExpertColor LV

## MAS LED MR16 ExpertColor 7.2-50W 930 10D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

### Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	GU5.3 [GU5.3]		
Nominal lifetime	40,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	930 [CCT of 3000K]	Line Frequency	- Hz
Beam Angle (Nom)	10 degree(s)	Input Frequency	- Hz
Luminous Flux	480 lm	Power Consumption	7.2 W
Luminous Intensity (Nom)	5,000 cd	Lamp Current (Nom)	800 mA
Color Designation	White (WH)	Wattage Equivalent	50 W
Correlated Color Temperature (Nom)	3000 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	66.67 lm/W	Warm-up time to 60% light	1 s
Color Consistency	<3	Power Factor (Fraction)	0.7
Color rendering index (CRI)	97	Voltage (Nom)	12 V
		Temperature	
		T-Case Maximum (Nom)	92 °C

## MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	MAS LED MR16 ExpertColor 7.2-50W 930 1000lm


Full product name	MAS LED MR16 ExpertColor 7.2-50W 930 10D
Full product code	871869657163700
Order code	929001242008
Material Nr. (12NC)	929001242008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696571637
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696571644

## Dimensional drawing




Product	D	C
MAS LED MR16 ExpertColor 7.2-50W 930 10D	51 mm	46 mm

## Photometric data




**Spectral Power Distribution Colour - MAS LED MR16 ExpertColor 7.2-50W**  
930 10D



General uniform lighting - MAS LED MR16 ExpertColor 7.2-50W 930 10D

## MASTER LEDspot ExpertColor LV

### Photometric data



Light Distribution Diagram - MAS LED MR16 ExpertColor 7.2-50W 930 10D

