



MASTER LEDspot ExpertColor LV

MAS LED MR16 ExpertColor 7.2-50W 927 36D


MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data

General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	GU5.3 [GU5.3]		
Nominal lifetime	40,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	927	Line Frequency	- Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	- Hz
Luminous Flux	450 lm	Power Consumption	7.2 W
Luminous Intensity (Nom)	1,350 cd	Lamp Current (Nom)	800 mA
Color Designation	Warm White (WW)	Wattage Equivalent	50 W
Correlated Color Temperature (Nom)	2700 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	62.50 lm/W	Warm-up time to 60% light	1 s
Color Consistency	<3	Power Factor (Fraction)	0.7
Color rendering index (CRI)	97	Voltage (Nom)	12 V
		Temperature	
		T-Case Maximum (Nom)	92 °C


MASTER LEDspot ExpertColor LV

Photometric data




Light Distribution Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 36D

Lifetime



Life Expectancy Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 36D



Lumen Maintenance Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 36D

