



Standard LED candles & lusters

LEDBulb 3.5-40W E27 6500K 100-240VG45_BR

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	3.5 W
Rated Lifetime (Hours)	15,000 hour(s)	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.5
Light Technical		Voltage (Nom)	100-240 V
Color Code	865 [CCT of 6500K]	Controls and Dimming	
Luminous Flux	350 lm	Dimmable	No
Color Designation	Cool Daylight	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Bulb Shape	G45
Color Consistency	<6	Product Data	
Color rendering index (CRI)	80	Order product name	LEDBulb 3.5-40W E27 6500K 100-240VG45_BR
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Standard LED candles & lusters

Full product name	LEDBulb 3.5-40W E27 6500K 100-240VG45_BR
Full product code	871869657645800
Order code	929001243411
Material Nr. (12NC)	929001243411
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8718696576458
Numerator - Packs per outer box	8
EAN/UPC - Case	8718696576465

Dimensional drawing



Product	D	C
LEDBulb 3.5-40W E27 6500K 100-240VG45_BR	45 mm	88 mm

