



CorePro LEDlinear MV



CorePro LED linear R7S 118mm 14-100W 830 D

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its ‘light all around’ design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Product data

General Information	
Cap base	R7s
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes

Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	1,600 lm
Colour designation	White (WH)
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	114.29 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input frequency	50 to 60 Hz
Power Consumption	14 W
Lamp current (nom.)	74 mA
Wattage equivalent	100 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	90 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb shape	Linear


Approval and Application	
Energy Efficiency Class	E
Energy-saving product	Yes
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	14 kWh

CorePro LEDlinear MV

EPREL registration number	465216
EyeComfort	Yes
Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	CorePro R7S 118mm 14-100W 830 D
Full product name	CorePro LED linear R7S 118mm 14-100W 830 D



Full EOC	871869657879700
Order code	57879700
Material no. (12 NC)	929001243702
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696578797
Numerator – packs per outer box	10
EAN/UPC – Case	8718696578803

Dimensional drawing




Product	D	C
CorePro R7S 118mm 14-100W 830 D	29 mm	118 mm

Photometric data



Spectral Power Distribution Colour - CorePro R7S 118mm 14-100W 830 D

General uniform lighting - CorePro R7S 118mm 14-100W 830 D



Light Distribution Diagram - CorePro R7S 118mm 14-100W 830 D

