



MASTER LEDtube EM/ Mains T8

MAS LEDtube 1200mm 16W865 T8 I

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

• –

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	2,100 lm
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	16 W
Lamp Current (Max)	77 mA
Lamp Current (Min)	68 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1,200 mm

MASTER LEDtube EM/Mains T8

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
Product Data	
Order product name	MAS LEDtube 1200mm 16W865 T8 I
Full product name	MAS LEDtube 1200mm 16W865 T8 I



Full product code	871869667640000
Order code	929001249208
Material Nr. (12NC)	929001249208
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696676400
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696676417

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm 16W865 T8 I	25.68 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data




Spectral Power Distribution Colour – MAS LEDtube 1200mm 16W865 T8 I

General uniform lighting – MAS LEDtube 1200mm 16W865 T8 I

MASTER LEDtube EM/Mains T8

Photometric data



Light Distribution Diagram - MAS LEDtube 1200mm 16W865 T8 I

