



CorePro LEDtube InstantFit HF

CorePro LEDtube HF 600mm 9W840 T8 G

CorePro LEDtube InstantFit HF is an affordable LED solution suitable for replacing T8 fluorescent lamps. It provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	9 W
Nominal lifetime	30,000 hour(s)	Lamp Current (Max)	400 mA
Switching Cycle	50,000	Lamp Current (Min)	200 mA
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.9
Color Code	840 [CCT of 4000K]	Voltage (Nom)	30-80 V
Beam Angle (Nom)	240 degree(s)	Temperature	
Luminous Flux	800 lm	Ambient temperature range	-20 °C to 45 °C
Color Designation	Cool White (CW)	T-Case Maximum (Nom)	60 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	88.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	83	Bulb Material	Glass
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	600 mm
Operating and Electrical			
Line Frequency	20000-80000 Hz		

CorePro LEDtube InstantFit HF

Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	12 kWh
Product Data	
Order product name	CorePro LEDtube HF 600mm 9W840 T8 G



Full product name	CorePro LEDtube HF 600mm 9W840 T8 G
Full product code	871869665217600
Order code	65217600
Material Nr. (12NC)	929001249502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696652176
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696652183

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 600mm 9W840 T8 G	27.9 mm	28 mm	589.8 mm	595.7 mm	604 mm

Photometric data




General uniform lighting - CorePro LEDtube HF 600mm 9W840 T8 G

Light Distribution Diagram - CorePro LEDtube HF 600mm 9W840 T8 G

CorePro LEDtube InstantFit HF

Photometric data



Spectral Power Distribution Colour - CorePro LEDtube HF 600mm 9W840 T8 G

