



CorePro LEDtube InstantFit HF

CorePro LEDtube HF 600mm 9W865 T8 G

CorePro LEDtube InstantFit HF is an affordable LED solution suitable for replacing T8 fluorescent lamps. It provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Starting Time (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.5 s
Nominal Lifetime (Nom)	30000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Voltage (Nom)	30-80 V
B50L70	30000 h		
Light Technical		Temperature	
Color Code	865 [CCT of 6500K]	T-Ambient (Max)	45 °C
Luminous Flux (Nom)	800 lm	T-Ambient (Min)	-20 °C
Luminous Flux (Rated) (Nom)	800 lm	T-Storage (Max)	65 °C
Correlated Color Temperature (Nom)	6500 K	T-Storage (Min)	-40 °C
Luminous Efficacy (rated) (Nom)	89.00 lm/W	T-Case Maximum (Nom)	60 °C
Color Consistency	<6	Controls and Dimming	
Color Rendering Index (Nom)	83	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing	
Operating and Electrical		Product Length	600 mm
Power (Rated) (Nom)	9 W	Approval and Application	
Lamp Current (Max)	400 mA	Energy Efficiency Label (EEL)	A
Lamp Current (Min)	200 mA	Energy Saving Product	Yes

CorePro LEDtube InstantFit HF

Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	12 kWh
Product Data	
Full product code	871869665219000
Order product name	CorePro LEDtube HF 600mm 9W865 T8 G
EAN/UPC - Product	8718696652190

Order code	929001249602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001249602
Net Weight (Piece)	0.160 kg



Dimensional drawing




CorePro LEDtube HF 600mm 9W865 T8 G

Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 600mm 9W865 T8 G	27.9 mm	28 mm	589.8 mm	595.7 mm	604 mm

Photometric data



MAS LED ExpertColor 7.2-50W MR16 GU5.3 930 36D



CorePro LEDtube InstantFit HF

