



Standard LED candles & lusters

LEDClassic 40W B35 E14 WW CL ND

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Operating and Electrical	
Cap-Base	E14 [E14]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	20,000	Power Consumption	4 W
Lighting Technology	LED	Lamp Current (Nom)	33 mA
EU RoHS compliant	Yes	Wattage Equivalent	40 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	827 [CCT of 2700K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	300 degree(s)	Power Factor (Fraction)	0.4
Luminous Flux	470 lm	Voltage (Nom)	220-240 V
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	2700 K	T-Case Maximum (Nom)	45 °C
Luminous Efficacy (rated) (Nom)	117.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Clear

Standard LED candles & lusters

Bulb Shape	B35 [B 35mm]
Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	LEDClassic 40W B35 E14 WW CL ND
Full product name	LEDClassic 40W B35 E14 WW CL ND
Full product code	871869679126400


Order code	929001258091
Material Nr. (12NC)	929001258091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696791264
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696791271

Dimensional drawing




Product	D	C
LEDClassic 40W B35 E14 WW CL ND	35 mm	97 mm

Photometric data



Spectral Power Distribution Colour - LEDClassic 40W B35 E14 WW CL ND



General uniform lighting - LEDClassic 40W B35 E14 WW CL ND

Light Distribution Diagram - LEDClassic 40W B35 E14 WW CL ND

Standard LED candles & lusters

