

Classic filament LEDbulbs

LED B35 1-25W E14 CL ND 865

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime (nom.)	25000 h
Switching cycle	20000X
Technical type	1-25W
Light Technical	
Colour code	865 [CCT of 6,500 K]
Luminous flux (nom.)	200 lm
Luminous flux (rated) (nom.)	200 lm
Colour designation	Cool Daylight
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	200.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	1 W
Lamp current (nom.)	10 mA
Wattage equivalent	25 W


Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	1 kWh
Product Data	
Full product code	871869665887100
Order product name	LED B35 1-25W E14 CL ND 865

Classic filament LEDbulbs

EAN/UPC – product	8718696658871
Order code	65887100
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001262502
Net weight (piece)	0.014 kg


Dimensional drawing




LED B35 1-25W E14 CL ND 865

Product	D	C
LED B35 1-25W E14 CL ND 865	35 mm	97 mm

Photometric data



LED 1-25W B35 E14 865 200lm



LEDBulb Candle and Lustré 1W E14 Clear 6500K

