



# Classic filament LEDbulbs

## LED A60 2-40W E27 CL ND 830

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	20000X
Technical type	2-40W

Light Technical	
Colour code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	400 lm
Luminous flux (rated) (nom.)	400 lm
Colour designation	White (WH)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	200.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	2 W
Lamp current (nom.)	19 mA
Wattage equivalent	40 W

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb finish	Clear (CL)

Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	2 kWh


Product Data	
Full product code	871869665889500
Order product name	LED A60 2-40W E27 CL ND 830

## Classic filament LEDbulbs

EAN/UPC – product	8718696658895
Order code	65889500
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001262602
Net weight (piece)	0.030 kg



### Dimensional drawing



LED A60 2-40W E27 CL ND 830

Product	D	C
LED A60 2-40W E27 CL ND 830	60 mm	104 mm

### Photometric data



LED Bulb 2W E27 A60 Clear 3000K

