



# Classic filament LEDbulbs

## LED A60 2-40W E27 CL ND 830

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information		Starting time (nom.)	
Cap base	E27 [ E27]		0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light (nom.)	1 s
Nominal lifetime (nom.)	25000 h	Power factor (nom.)	0.5
Switching cycle	20,000X	Voltage (Nom)	220-240 V
Technical type	2-40W	<b>Temperature</b>	
<b>Light Technical</b>		T-Case maximum (nom.)	50 °C
Colour code	830 [ CCT of 3,000 K]	<b>Controls and Dimming</b>	
Luminous flux (nom.)	400 lm	Dimmable	No
Colour designation	White (WH)	<b>Mechanical and Housing</b>	
Correlated Colour Temperature (Nom)	3000 K	Bulb finish	Clear
Luminous efficacy (rated) (nom.)	200.00 lm/W	<b>Approval and Application</b>	
Colour consistency	<6	Energy efficiency label (EEL)	Not applicable
Color rendering index (nom.)	80	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Suitable for accent lighting	No
<b>Operating and Electrical</b>		Energy Consumption kWh/1000 h	2 kWh
Input frequency	50 to 60 Hz	<b>Product Data</b>	
Power (Rated) (Nom)	2 W	Full product code	871869665889500
Lamp current (nom.)	19 mA		
Wattage equivalent	40 W		

# Classic filament LEDbulbs

Order product name	LED A60 2-40W E27 CL ND 830
EAN/UPC – product	8718696658895
Order code	65889500
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001262602
Net weight (piece)	0.030 kg


## Dimensional drawing

Product drawing showing dimensions D and C.


Product	D	C
LED A60 2-40W E27 CL ND 830	60 mm	104 mm

LED A60 2-40W E27 CL ND 830

## Photometric data



LED 2-40W A60 E27 830



LED Bulb 2W E27 A60 Clear 3000K

