



Classic filament LEDbulbs

LED A60 2-40W E27 CL ND 830

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	2 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	19 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	1 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical			
Color Code	830 [CCT of 3000K]	Temperature	
Luminous Flux	400 lm	T-Case Maximum (Nom)	50 °C
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	200.00 lm/W	Dimmable	No
Color Consistency	<6		
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Clear
		Bulb Shape	A60 [A 60mm]
Operating and Electrical			
Line Frequency	50 to 60 Hz	Approval and Application	
Input Frequency	50 to 60 Hz	Energy Saving Product	Yes

Classic filament LEDbulbs

Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
Product Data	
Order product name	LED A60 2-40W E27 CL ND 830
Full product name	LED A60 2-40W E27 CL ND 830
Full product code	871869665889500
Order code	929001262602



Material Nr. (12NC)	929001262602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696658895
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696658901

Dimensional drawing



Product	D	C
LED A60 2-40W E27 CL ND 830	60 mm	104 mm

Photometric data



Spectral Power Distribution Colour - LED A60 2-40W E27 CL ND 830

General uniform lighting - LED A60 2-40W E27 CL ND 830

