



# Classic filament LEDbulbs

## LED A60 3-60W E27 CL ND 830

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	25000 h
Switching cycle	20000X
Technical type	3-60W
Light Technical	
Colour code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	600 lm
Luminous flux (rated) (nom.)	600 lm
Colour designation	White (WH)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	200.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	3 W
Lamp current (nom.)	28 mA
Wattage equivalent	60 W


Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	3 kWh
Product Data	
Full product code	871869665893200
Order product name	LED A60 3-60W E27 CL ND 830

# Classic filament LEDbulbs

EAN/UPC – product	8718696658932
Order code	65893200
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001262802
Net weight (piece)	0.030 kg



## Dimensional drawing




LED A60 3-60W E27 CL ND 830

Product	D	C
LED A60 3-60W E27 CL ND 830	60 mm	104 mm

## Photometric data



LED 3-60W A60 E27 830 600lm CL ND



## Classic filament LEDbulbs

