



LED Highbay

165HB/LED/840/ND NB UDL 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Base	EX39 [Exclusionary Mogul Screw]
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	165-400W
Light Technical	
Color Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	60 °
Initial lumen (Nom)	19000 lm
Luminous Flux (Rated) (Nom)	19000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115.15 lm/W
Color Consistency	ANSI 4000K
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	165 W
Lamp Current (Nom)	3650 mA

Wattage Equivalent	400 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.6
Voltage (Nom)	/ V

Temperature	
T-Case Maximum (Nom)	85 °C

Controls and Dimming	
Dimmable	No

Product Data	
Order product name	165HB/LED/840/ND NB UDL 2/1
EAN/UPC - Product	046677465650
Order code	465658
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001265304
Net Weight (Piece)	1.300 kg

LED Highbay



Dimensional drawing



Product	D	C
165HB/LED/840/ND NB UDL 2/1	209.7 mm	245.7 mm


Bulb 135W-400W 16000lm 60D 4000K E39XND

Photometric data



NAM Highbay 165W-400W 4000K 60D E39X UDL

NAM Highbay 165W EX39 4000K 60-120D NB WB UDL




NAM Highbay 165W EX39 4000K 60D NB UDL

LED Highbay

Lifetime



NAM Highbay 165W EX39 4000K 60-120D DL UDL



NAM Highbay 165W EX39 4000K 60-120D DL UDL

