

# Classic filament LEDbulbs

## CLA LEDBulb DT 4.5-40W A60 B22 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data


<b>General Information</b>		<b>Lamp Current (Nom)</b>		24 mA
Cap-Base	B22 [B22]	<b>Wattage Equivalent</b>		40 W
Nominal lifetime	15,000 hour(s)	<b>Starting Time (Nom)</b>		0.5 s
Switching Cycle	20,000	<b>Warm-up time to 60% light</b>		0.5 s
Lighting Technology	LED	<b>Power Factor (Fraction)</b>		0.8
EU RoHS compliant	Yes	<b>Voltage (Nom)</b>		220-240 V
<b>Light Technical</b>		<b>Temperature</b>		
Color Code	822-827 [tunable warm white]	<b>T-Case Maximum (Nom)</b>		60 °C
Luminous Flux	470 lm	<b>Controls and Dimming</b>		
Color Designation	Warm White (WW)	<b>Dimmable</b>		Yes
Luminous Efficacy (rated) (Nom)	94.00 lm/W	<b>Mechanical and Housing</b>		
Color Consistency	<6	<b>Bulb Finish</b>		Clear
Color rendering index (CRI)	80	<b>Bulb Shape</b>		A60 [A 60mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Approval and Application</b>		
<b>Operating and Electrical</b>		<b>Energy Saving Product</b>		Yes
Line Frequency	50 to 60 Hz	<b>Suitable For Accent Lighting</b>		No
Input Frequency	50 to 60 Hz			
Power Consumption	4.5 W			

Classic filament LEDbulbs

Energy Consumption kWh/1000 h	5 kWh
Product Data	
Order product name	CLA LEDBulb DT 4.5-40W A60 B22 CL
Full product name	CLA LEDBulb DT 4.5-40W A60 B22 CL
Full product code	871869665678500
Order code	929001268402



Material Nr. (12NC)	929001268402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696656785
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696656792

Dimensional drawing




Product	D	C
CLA LEDBulb DT 4.5-40W A60 B22 CL	60 mm	110 mm

Photometric data



Light Distribution Diagram - CLA LEDBulb DT 4.5-40W A60 B22 CL

General uniform lighting - CLA LEDBulb DT 4.5-40W A60 B22 CL



Spectral Power Distribution Colour - CLA LEDBulb DT 4.5-40W A60 B22 CL

## Classic filament LEDbulbs

