



# Essential LEDspot MR16

## ESS LED MR16 3-35W 36D 830 100-240V

Essential LEDspots MR16 are compatible with most existing fixtures with a GU5.3 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots MR16 deliver significant energy savings and minimize initial investment.

### Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	230 lm
Luminous Intensity (Nom)	380 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	76.67 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	3 W
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100-240 V

Temperature	
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]


Approval and Application	
Suitable For Accent Lighting	Yes

# Essential LEDspot MR16

Product Data	
Order product name	ESS LED MR16 3-35W 36D 830 100-240V
Full product name	ESS LED MR16 3-35W 36D 830 100-240V
Order code	929001274212
Material Nr. (12NC)	929001274212
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	046677466879
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677466874

## Dimensional drawing




Product	D	C
ESS LED MR16 3-35W 36D 830 100-240V	51 mm	49 mm


## Photometric data



Spectral Power Distribution Colour - ESS LED MR16 3-35W 36D 830 100-240V




General uniform lighting - ESS LED MR16 3-35W 36D 830 100-240V




Light Distribution Diagram - ESS LED MR16 3-35W 36D 830 100-240V

Essential LEDspot MR16

Lifetime



Life Expectancy Diagram - ESS LED MR16 3-35W 36D 830 100-240V



Lumen Maintenance Diagram - ESS LED MR16 3-35W 36D 830 100-240V

