



Decorative LED bulbs

LED Classic CM A60 48W WW E27 CL ND SRT4

The new Deco collection (bulb) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.


Product data

General Information		Temperature	
Cap base	E27 [E27]	Warm-up time to 60% light (nom.)	1 s
Nominal lifetime (nom.)	15000 h	Power factor (nom.)	0.5
Switching cycle	20000X	Voltage (Nom)	220-240 V
Technical type	5.5-48W	Temperature	
Light Technical		T-Case maximum (nom.)	60 °C
Colour Code	827 [CCT of 2,700 K]	Controls and Dimming	
Lamp Luminous Flux 25°C EL (Nom)	620 lm	Dimmable	No
Lamp Luminous Flux (Nom)	620 lm	Approval and Application	
Colour Designation	Warm white (WW)	Energy efficiency label (EEL)	A++
Colour Temperature, horizontal (Nom)	2700 K	Energy Consumption kWh/1000 h	6 kWh
Lamp Luminous Efficacy EM (Nom)	112.73 lm/W	Product Data	
Colour consistency	<6	Full product code	871869666869601
Colour Rendering Index,horiz (Nom)	80	Order product name	LED Classic CM A60 48W WW E27 CL ND SRT4
LLMF at end of nominal lifetime (nom.)	70 %	EAN/UPC – product	8718696668696
Operating and Electrical		Order code	929001276558
Input frequency	50 to 60 Hz	Numerator – quantity per pack	1
Power (Rated) (Nom)	5.5 W	Numerator – packs per outer box	4
Lamp current (nom.)	50 mA	Material no. (12NC)	929001276558
Starting time (nom.)	0.5 s		

Decorative LED bulbs

Net weight (piece) 0.030 kg


Dimensional drawing




FLT A60 230V 530lm 2700K E27 ND Mirror

Product	D	C
LED Classic CM A60 48W WW E27 CL ND SRT4	60 mm	104 mm


Photometric data



LEDbulb Classic CM 48W E27 A60 827 ND





LEDbulb Classic CM 48W E27 A60 827 ND



LEDbulb Classic CM 30W E27 A60 827 ND

Decorative LED bulbs

Lifetime



LEDbulb Classic CM 48W E27 A60 Mirror Crown 827 DIM

LEDbulb Classic CM 48W E27 A60 Mirror Crown 827 DIM

