

Essential LEDtube

LEDtube HO 1200mm 20W 740 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General information		Voltage (Nom)	
Cap base	G13 [Medium Bi-Pin Fluorescent]	220-240 V	
EU RoHS compliant	Yes	Temperature	
Nominal lifetime (nom.)	15000 h	T-ambient (max.)	45 °C
Switching cycle	50000	T-ambient (min.)	-20 °C
Light technical		T storage (max.)	65 °C
Colour Code	740 [CCT of 4,000 K]	T storage (min.)	-40 °C
Technical Beam Angle (Nom)	240 °	T-Case maximum (nom.)	65 °C
Lamp Luminous Flux 25°C EL (Nom)	2100 lm	Controls and dimming	
Colour Designation	Cool White (CW)	Dimmable	No
Colour Temperature, horizontal (Nom)	4000 K	Mechanical and housing	
Lamp Luminous Efficacy EM (Nom)	105.00 lm/W	Product length	1200 mm
Colour consistency	<7	Bulb shape	Tube, double-ended
Colour Rendering Index,horiz (Nom)	70	Approval and application	
LLMF at end of nominal lifetime (nom.)	70 %	Energy-saving product	Yes
Operating and electrical		Approval marks	RoHS compliance KEMA Keur certificate
Input frequency	50 to 60 Hz	Energy consumption kWh/1,000 hours	20 kWh
Power (Rated) (Nom)	20 W	Product data	
Starting time (nom.)	0.5 s	Full product code	871869667434500
Warm-up time to 60% light (nom.)	0.5 s		
Power factor (nom.)	0.5		

Essential LEDtube

Order product name	LEDtube HO 1200mm 20W 740 T8 AP I G
EAN/UPC – product	8718696674345
Order code	929001277208
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10

SAP material	929001277208
Net Weight (Piece)	0.215 kg


Dimensional drawing




LEDtube HO 1200mm 20W 740 T8 AP I G

Product	D1	D2	A1	A2	A3
LEDtube HO 1200mm 20W 740 T8 AP I G	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


Photometric data



LEDtube HO 20W G13 740 T8 AP I G





LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 740 T8 AP I G



Essential LEDtube

Lifetime




LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

Essential LEDtube

