



# CorePro LED PLC 2P

## LED PLC 8.5W 865 2P G24d-3

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

### Product data


General information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G24D-3 [ G24d-3]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.9
Nominal Lifetime (Nom)	30000 h	Voltage (Nom)	220-240 V
Switching Cycle	50000X	<b>Temperature</b>	
<b>Light technical</b>		T-Ambient (Max)	35 °C
Color Code	865 [ CCT of 6500K]	T-Ambient (Min)	-20 °C
Beam Angle (Nom)	120 °	T-Storage (Max)	65 °C
Luminous Flux (Nom)	1000 lm	T-Storage (Min)	-40 °C
Color Designation	Cool Daylight	T-Case Maximum (Nom)	75 °C
Correlated Color Temperature (Nom)	6500 K	<b>Controls and dimming</b>	
Luminous Efficacy (rated) (Nom)	117.00 lm/W	Dimmable	No
Color Consistency	<6	<b>Mechanical and housing</b>	
Color Rendering Index (Nom)	83	Product Length	200 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, single-ended
<b>Operating and electrical</b>		<b>Approval and application</b>	
Input Frequency	50 to 60 Hz	Energy Saving Product	Yes
Power (Nom)	8.5 W	Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Lamp Current (Max)	43 mA		
Lamp Current (Min)	33 mA		
Starting Time (Nom)	0.5 s		

# CorePro LED PLC 2P

Energy Consumption kWh/1000 h	11 kWh
<b>Product data</b>	
Full product code	871869666995200
Order product name	LED PLC 8.5W 865 2P G24d-3
EAN/UPC - Product	8718696669952
Order code	929001280108

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001280108
Net Weight (Piece)	0.090 kg


## Dimensional drawing




LED PLC 8.5W 865 2P G24d-3

Product	D1	D2	A1	A2	A3
LED PLC 8.5W 865 2P G24d-3	24.3 mm	28.4 mm	128.8 mm	148 mm	170.6 mm


## Photometric data



LEDtube PLC 100mm 9W G24D-3 865 1000lm



LEDtube PLC 100mm 9W G24D-3 865 1000lm



LEDtube PLC 100mm 9W G24D-3 865 1000lm


# CorePro LED PLC 2P

## Lifetime




LEDtube PLC 100mm 9W G24D-3 830 950lm

LEDtube PLC 100mm 9W G24D-3 830 950lm



LEDtube PLC 100mm 9W G24D-3 830 950lm

LEDtube PLC 100mm 9W G24D-3 830 950lm



LEDtube PLC 100mm 9W G24D-3 830 950lm

## CorePro LED PLC 2P

