



# MasterConnect LEDtube InstantFit T8

## 14T8/48-3000 IF 10/1 EasySmart

Philips MasterConnect LEDtube InstantFit T8 lamp, which is Interact Ready, enables an easy upgrade to a connected lighting system without re-wiring the fixtures. The 2.4GHz mesh networking technology allows integration with a variety of control device, such as sensor and switch. It also offers secure and reliable communication towards the Interact IoT platform or verified third party systems. The result? Greater energy savings, various control possibilities and a more adaptable space!

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Main Application	Industrial
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h

Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	2000 lm
Luminous Flux (Rated) (Nom)	2000 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W

Lamp Current (Max)	240 mA
Lamp Current (Min)	130 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277, 347 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	40 °C

Controls and Dimming	
Dimmable	Wireless Dim

# MasterConnect LEDtube InstantFit T8


## Mechanical and Housing

Product Length	1200 mm
<b>Approval and Application</b>	
Energy Efficiency Label (EEL)	Not applicable
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

## Product Data

Order product name	14T8/48-3000 IF 10/1 EasySmart
EAN/UPC - Product	046677466459
Order code	929001281104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001281104
Net Weight (Piece)	0.230 kg


## Dimensional drawing




14T8/48-3000 IF 10/1 EasySmart

Product	D1	D2	A1	A2	A3
14T8/48-3000 IF 10/1 EasySmart	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm

## Photometric data




LEDtube 1200mm 14W G13 830 2000lm



LEDtube 1200mm 14W G13 2000lm

# MasterConnect LEDtube InstantFit T8


## Photometric data




General Information 41 Philips Lighting B.V. Page 17

LEDtube 1200mm 14W G13 830 2000lm

## Lifetime



LEDtube 1200mm 14W G13 2000lm



LEDtube 1200mm 14W G13 2000lm

