



Standard LED spots GU10

LEDspot GU10 5-50W 865 36D 220-240V PF

Standard and Glass LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. Standard and Glass LEDspots are the perfect solution for your basic lighting needs: they provide the beautiful light and performance you expect from the LED technology at an affordable price.

Product data

| General Information | |
|---------------------|----------------|
| Cap-Base | GU10 [GU10] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |

| Light Technical | |
|---------------------------------------|--------------------|
| Color Code | 865 [CCT of 6500K] |
| Beam Angle (Nom) | 36 degree(s) |
| Luminous Flux | 430 lm |
| Luminous Intensity (Nom) | 900 cd |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6500 K |
| Luminous Efficacy (rated) (Nom) | 70.00 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| Operating and Electrical | |
|---------------------------|-------------|
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 5 W |
| Lamp Current (Nom) | 40 mA |
| Wattage Equivalent | 50 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.5 |
| Voltage (Nom) | 220-240 V |

| Temperature | |
|----------------------|-------|
| T-Case Maximum (Nom) | 80 °C |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

Standard LED spots GU10


| Mechanical and Housing | |
|------------------------|-------------------------|
| Bulb Shape | PAR16 [PAR 2 inch/50mm] |

| Approval and Application | |
|-------------------------------|-------|
| Suitable For Accent Lighting | Yes |
| Energy Consumption kWh/1000 h | 5 kWh |

| Product Data | |
|--------------------|--|
| Order product name | LEDspot GU10 5-50W 865 36D 220-240V PF |
| Full product name | LEDspot GU10 5-50W 865 36D 220-240V PF |

| | |
|---------------------------------|-----------------|
| Full product code | 871869667424600 |
| Order code | 929001281611 |
| Material Nr. (12NC) | 929001281611 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696674246 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718696674253 |

Dimensional drawing



| Product | D | C |
|--|-------|-------|
| LEDspot GU10 5-50W 865 36D 220-240V PF | 50 mm | 54 mm |

