



# Standard LED candles & lusters

## LEDBulb 6.5-40W E14 6500K 220V P50\_AU

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data


General Information		Operating and Electrical	
Cap-Base	E14 [E14]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 h	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	6.5 W
Lighting Technology	LED	Wattage Equivalent	40 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	865 [CCT of 6500K]	Power Factor (Fraction)	0.5
Beam Angle (Nom)	150 degree(s)	Voltage (Nom)	220-240 V
Luminous Flux	600 lm	Temperature	
Color Designation	Cool Daylight	T-Case Maximum (Nom)	90 °C
Correlated Color Temperature (Nom)	6500 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	95.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Standard LED candles & lusters

Bulb Shape	P50 [P 50mm]
Product Data	
Order product name	LEDBulb 6.5-40W E14 6500K 220V P50_AU
Full product name	LEDBulb 6.5-40W E14 6500K 220V P50_AU
Full product code	871869667706301
Order code	929001283679

Material Nr. (12NC)	929001283679
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696677063
Numerator - Packs per outer box	3
EAN/UPC - Case	8718696733868

Dimensional drawing



Product	D	C
LEDBulb 6.5-40W E14 6500K 220V P50_AU	50 mm	95 mm

