



CorePro LEDspot MV

Corepro LEDspot 550lm GU10 840 120D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	550 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5 W


Lamp Current (Nom)	41 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR16 [PAR 2 inch/50mm]
Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes
Product Data	
Order product name	Corepro LEDspot 550lm GU10 840 120D

CorePro LEDspot MV

Full product name	Corepro LEDspot 550lm GU10 840 120D
Full product code	871869668690400
Order code	929001297332
Material Nr. (12NC)	929001297332
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718696686904
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696686911

Dimensional drawing




Product	D	C
Corepro LEDspot 550lm GU10 840 120D	50 mm	55 mm


Photometric data



Spectral Power Distribution Colour – Corepro LEDspot 550lm GU10 840 120D




Light Distribution Diagram – Corepro LEDspot 550lm GU10 840 120D




General uniform lighting – Corepro LEDspot 550lm GU10 840 120D

CorePro LEDspot MV

Lifetime



Life Expectancy Diagram - Corepro LEDspot 550lm GU10 840 120D



Lumen Maintenance Diagram - Corepro LEDspot 550lm GU10 840 120D

