



MASTER LEDtube EM/ Mains

MAS LEDtube 1200mm UO 16W 830 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	50000 h
Switching cycle	200000X
B50L70	50000 h

Light Technical	
Colour Code	830 [CCT of 3,000 K]
Technical Beam Angle (Nom)	160 °
Lamp Luminous Flux 25°C EL (Nom)	2300 lm
Lamp Luminous Flux (Nom)	2300 lm
Rated beam angle	160 °
Colour Temperature, horizontal (Nom)	3000 K
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz

Power (Rated) (Nom)	16 W
Lamp current (max.)	75 mA
Lamp current (min.)	68 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V

Temperature	
T ambient (max.)	35 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	55 °C

Controls and Dimming	
Dimmable	No

MASTER LEDtube EM/Mains

Mechanical and Housing

Product length 1200 mm

Approval and Application

Energy efficiency label (EEL) A++
 Energy-saving product Yes
 Approval marks CE marking RoHS compliance KEMA Keur certificate
 Energy Consumption kWh/1000 h 16 kWh

Product Data


Full product code 871869668736900

Order product name MAS LEDtube 1200mm UO 16W 830 T8
 EAN/UPC – product 8718696687369
 Order code 929001297802
 Numerator – quantity per pack 1
 Numerator – packs per outer box 10
 Material no. (12NC) 929001297802
 Net weight (piece) 0.251 kg

Warnings and Safety

• -



Dimensional drawing



TLED 4ft 16W-36W 2300lm 160D 3000K G13ND

Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm UO 16W 830 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data



LEDtube 1200mm UO 16W 830 T8

LEDtube 1200mm UO 16W 830 T8

MASTER LEDtube EM/Mains

Photometric data



LEDtube 600mm 1200mm 1500mm UO T8

Lifetime



LEDtube 600mm 1200mm 1500mm UO T8



LEDtube 600mm 1200mm 1500mm UO T8

