



Essential LEDtube

LEDtube HO 600mm 10W 730 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	220-240 V	
EU RoHS compliant	Yes	Temperature	
Nominal Lifetime (Nom)	15000 h	T-Ambient (Max)	45 °C
Switching Cycle	50000	T-Ambient (Min)	-20 °C
Light technical		T-Storage (Max)	65 °C
Color Code	730 [CCT of 3000K]	T-Storage (Min)	-40 °C
Beam Angle (Nom)	240 °	T-Case Maximum (Nom)	65 °C
Luminous Flux (Nom)	950 lm	Controls and dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Mechanical and housing	
Luminous Efficacy (rated) (Nom)	95.00 lm/W	Product Length	600 mm
Color Consistency	<7	Bulb Shape	Tube, double-ended
Color Rendering Index (Nom)	70	Approval and application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and electrical		Approval Marks	RoHS compliance KEMA Keur certificate
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	10 kWh
Power (Nom)	10 W	Product data	
Starting Time (Nom)	0.5 s	Full product code	871869668766600
Warm Up Time to 60% Light (Nom)	0.5 s		
Power Factor (Nom)	0.5		

Essential LEDtube

Order product name	LEDtube HO 600mm 10W 730 T8 AP I G
EAN/UPC - Product	8718696687666
Order code	929001299908
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001299908
Net Weight (Piece)	0.120 kg


Dimensional drawing




LEDtube HO 600mm 10W 730 T8 AP I G

Product	D1	D2	A1	A2	A3
LEDtube HO 600mm 10W 730 T8 AP I G	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


Photometric data



LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G





General Uniform Lighting

LEDtube HO 10W G13 730 T8 AP I G



Essential LEDtube

Lifetime




LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

Essential LEDtube

