



MASTER LEDspot ExpertColor LV

MAS MR16 ExpertColor7.2-50W 940 36D EZ10

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data

General Information	
Cap-Base	EZ10 [EZ10]
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	480 lm
Luminous Intensity (Nom)	1,450 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	66.67 lm/W
Color Consistency	<3
Color rendering index (CRI)	97


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	7.2 W
Lamp Current (Nom)	800 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	92 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	MAS MR16 ExpertColor7.2-50W 940 36D EZ10



Full product name	MAS MR16 ExpertColor7.2-50W 940 36D EZ10
Full product code	871869669240000
Order code	929001303118
Material Nr. (12NC)	929001303118
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696692400
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696692417

Dimensional drawing



Product	D	C
MAS MR16 ExpertColor7.2-50W 940 36D EZ10	51 mm	59 mm

Photometric data



Accent Lighting Spots - MAS MR16 ExpertColor7.2-50W 940 36D EZ10

Light Distribution Diagram - MAS MR16 ExpertColor7.2-50W 940 36D EZ10


MASTER LEDspot ExpertColor LV

Photometric data




Spectral Power Distribution Colour - MAS MR16 ExpertColor7.2-50W 940 36D EZ10

Lifetime



Life Expectancy Diagram - MAS MR16 ExpertColor7.2-50W 940 36D EZ10



Lumen Maintenance Diagram - MAS MR16 ExpertColor7.2-50W 940 36D EZ10

