



# Standard LED bulbs

## Standard LEDBulb LEDBulb 5-50W E27 830 220-240V 1PF/10

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data

General Information	
Cap-Base	E27 [ E27]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	5-50W

Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	150 °
Luminous Flux (Nom)	470 lm
Luminous Flux (Rated) (Nom)	470 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	94.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W

Temperature	
T-Case Maximum (Nom)	80 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted

Approval and Application	
Energy Efficiency Label (EEL)	A+


Product Data	
Full product code	871869670145400

# Standard LED bulbs

<b>Order product name</b>	Standard LEDBulb LEDBulb 5-50W E27 830 220-240V 1PF/10
<b>EAN/UPC - Product</b>	8718696701454
<b>Order code</b>	929001304511
<b>Numerator - Quantity Per Pack</b>	1

<b>Numerator - Packs per outer box</b>	10
<b>Material Nr. (12NC)</b>	929001304511
<b>Net Weight (Piece)</b>	0.060 kg


## Dimensional drawing




A60 220-240V 5W-40W 470lm 3000K E27 ND

Product	D	C
Standard LEDBulb LEDBulb 5-50W E27 830 220-240V 1PF/10	60 mm	110 mm


## Photometric data



CorePro LEDbulb 40W E27 830 FR A60




CorePro LEDbulb 40W E27 830 FR A60




CorePro LEDbulb 40W E27 830 FR A60

## Standard LED bulbs

### Lifetime



LEDbulb 40W E27 830 FR A60



LEDbulb 40W E27 830 FR A60

