



# Standard LED spots GU10

## LEDspot 25W GU10 2700K 100-240V 36D ND

Standard and Glass LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. Standard and Glass LEDspots are the perfect solution for your basic lighting needs: they provide the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	250 lm
Luminous Intensity (Nom)	520 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	83.33 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3 W
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100-240 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR16 [PAR 2 inch/50mm]

## Standard LED spots GU10

### Approval and Application


Suitable For Accent Lighting Yes

### Product Data

Order product name	LEDspot 25W GU10 2700K 100-240V 36D ND
Full product name	LEDspot 25W GU10 2700K 100-240V 36D ND
Full product code	871869669563000
Order code	929001306371

Material Nr. (12NC)	929001306371
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696695630
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696695647

### Dimensional drawing



Product	D	C
LEDspot 25W GU10 2700K 100-240V 36D ND	50 mm	53 mm

