



Corepro InstantFit (UL Type-A) T8

35T8/96-3500 IF FA8 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data


General Information		Color Consistency	
Cap-Base	FA8 [FA8]	Color rendering index (CRI)	82
Nominal lifetime	50,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	70 %
Switching Cycle	50,000	Operating and Electrical	
Lighting Technology	LED	Line Frequency	50000-64000 Hz
EU RoHS compliant	Yes	Input Frequency	50000-64000 Hz
Light Technical		Power Consumption	35 W
Color Code	835 [CCT of 3500K]	Lamp Current (Max)	260 mA
Beam Angle (Nom)	180 degree(s)	Lamp Current (Min)	160 mA
Luminous Flux	4,000 lm	Wattage Equivalent	60 W
Color Designation	White (WH)	Warm-up time to 60% light	0.5 s
Correlated Color Temperature (Nom)	3500 K	Power Factor (Fraction)	0.9
Luminous Efficacy (rated) (Nom)	114.00 lm/W	Voltage (Nom)	280-410 V

Corepro InstantFit (UL Type-A) T8

UL Type	UL Type A
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	113 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	94-1/2 inch
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes



Approval Marks	UL certificate
Energy Consumption kWh/1000 h	- kWh
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	35T8/96-3500 IF FA8 10/1
Full product name	35T8/96-3500 IF FA8 10/1
Order code	469247
Material Nr. (12NC)	929001307804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677472573
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677469240

Dimensional drawing



Product	D	A1	A2	A3
35T8/96-3500 IF FA8 10/1	1-1/8 inch	93-3/16 inch	93-9/16 inch	93-7/8 inch

Photometric data




General uniform lighting - 35T8/96-3500 IF FA8 10/1

Spectral Power Distribution Colour - 35T8/96-3500 IF FA8 10/1

General uniform lighting - 35T8/96-3500 IF FA8 10/1


Corepro InstantFit (UL Type-A) T8

Photometric data




Light Distribution Diagram - 35T8/96-3500 IF FA8 10/1

Lifetime



Life Expectancy Diagram - 35T8/96-3500 IF FA8 10/1



Lumen Maintenance Diagram - 35T8/96-3500 IF FA8 10/1

