

# T8

## 7T8 LED/24-3500 IF 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

### Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Input Frequency	20000-120000 Hz
Nominal lifetime	50,000 hour(s)	Power Consumption	7 W
Switching Cycle	50,000	Lamp Current (Max)	240 mA
Lighting Technology	LED	Lamp Current (Min)	80 mA
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.1 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	120-277, 347 V
Light Technical		Temperature	
Color Code	835 [CCT of 3500K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	180 degree(s)	T-Case Maximum (Nom)	50 °C
Luminous Flux	1,050 lm		
Color Designation	White (WH)	Controls and Dimming	
Correlated Color Temperature (Nom)	3500 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	150.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	82	Product Length	600 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical			
Line Frequency	20000-120000 Hz		

# T8

## Approval and Application


Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh

## Product Data

Order product name	7T8 LED/24-3500 IF 10/1
Full product name	7T8 LED/24-3500 IF 10/1



Order code	469288
Material Nr. (12NC)	929001310904
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677472283
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677469288

## Dimensional drawing




Product	D1	D2	A1	A2	A3
7T8 LED/24-3500 IF 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm

## Photometric data



General uniform lighting - 7T8 LED/24-3500 IF 10/1



Light Distribution Diagram - 7T8 LED/24-3500 IF 10/1



Spectral Power Distribution Colour - 7T8 LED/24-3500 IF 10/1

# T8

## Lifetime



Life Expectancy Diagram - 7T8 LED/24-3500 IF 10/1

Lumen Maintenance Diagram - 7T8 LED/24-3500 IF 10/1

