



T8

9T8 LED/36-3000 IF 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.


Product data

General Information		
Base	G13 [Medium Bi-Pin Fluorescent]	
EU RoHS compliant	Yes	
Nominal Lifetime (Nom)	50000 h	
Switching Cycle	50000X	
Light Technical		
Color Code	830 [CCT of 3000K]	
Initial lumen (Nom)	1100 lm	
Correlated Color Temperature (Nom)	3000 K	
Color Consistency	<6	
Color Rendering Index (Nom)	82	
LLMF At End Of Nominal Lifetime (Nom)	70 %	
Operating and Electrical		
Input Frequency	20000-120000 Hz	
Power (Rated) (Nom)	9 W	
Lamp Current (Max)	180 mA	
Lamp Current (Min)	60 mA	
Starting Time (Nom)	0.5 s	
Warm Up Time to 60% Light (Nom)		0.1 s
Power Factor (Nom)		0.9
Voltage (Nom)		120-277, 347 V
Temperature		
T-Ambient (Max)		45 °C
T-Ambient (Min)		-20 °C
T-Storage (Max)		65 °C
T-Storage (Min)		-40 °C
T-Case Maximum (Nom)		50 °C
Controls and Dimming		
Dimmable		No
Mechanical and Housing		
Product Length		900 mm
Approval and Application		
Energy Efficiency Label (EEL)		Not applicable
Energy Saving Product		Yes

Approbation Marks	UL certificate RoHS compliance
Product Data	
Order product name	9T8 LED/36-3000 IF 10/1
EAN/UPC - Product	046677472313
Order code	469320
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001311304
Net Weight (Piece)	0.170 kg
Model Number	9290013113


Dimensional drawing




TLED 3ft 900mm 10.5-25W 1100lm 3000K ND

Product	D1	D2	A1	A2	A3
9T8 LED/36-3000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm

Photometric data




LEDtube 900mm 9W G13 830 1100lm




LEDtube 600mm 7W G13

Lifetime



LEDtube 600mm 7W G13



LEDtube 600mm 7W G13

