



# Corepro InstantFit (UL Type-A) T8

## 35T8/96-4000 IF FA8 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

#### **Product data**

General Information			
Cap-Base	FA8		
Nominal lifetime	50,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical			
Color Code	840 [CCT of 4000K]		
Beam Angle (Nom)	180 degree(s)		
Luminous Flux	4,200 lm		
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	120.00 lm/W		

Color Consistency	<6		
Color rendering index (CRI)	82		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50000-64000 Hz		
Input Frequency	50000-64000 Hz		
Power Consumption	35 W		
Lamp Current (Max)	260 mA		
Lamp Current (Min)	160 mA		
Wattage Equivalent	60 W		
Warm-up time to 60% light	0.5 s		
Power Factor (Fraction)	0.9		
Voltage (Nom)	280-410 V		


Datasheet, 2024, February 26 data subject to change

# Corepro InstantFit (UL Type-A) T8

UL Type	UL Type A		
Temperature			
Ambient temperature range	-20 °C to 45 °C		
T-Case Maximum (Nom)	45 °C		
Controls and Dimming			
Dimmable	No		
Mechanical and Housing			
Bulb Finish	Frosted		
Bulb Material	Plastic		
Product Length	2,400 mm		
Bulb Shape	Т8		
Approval and Application			
Energy Saving Product	Yes		


Approval Marks	UL certificate		
Energy Consumption kWh/1000 h	- kWh		
Application Conditions			
can it be used in closed luminaires	Yes		
Product Data			
Order product name	35T8/96-4000 IF FA8 10/1		
Full product name	35T8/96-4000 IF FA8 10/1		
Order code	929001314604		
Material Nr. (12NC)	929001314604		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	046677472580		
Numerator - Packs per outer box	10		
EAN/UPC - Case	50046677469257		


### Dimensional drawing



Product	D	A1	A2	A3
35T8/96-4000 IF FA8 10/1	27.9 mm	2,366.9 mm	2,375.2 mm	2,383.5 mm

#### Photometric data






Spectral Power Distribution Colour - 35T8/96-4000 IF FA8 10/1

General uniform lighting - 35T8/96-4000 IF FA8 10/1


## Corepro InstantFit (UL Type-A) T8


#### Photometric data



Light Distribution Diagram - 35T8/96-4000 IF FA8 10/1

#### Lifetime





Life Expectancy Diagram - 35T8/96-4000 IF FA8 10/1

Lumen Maintenance Diagram - 35T8/96-4000 IF FA8 10/1



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.