



Classic filament LEDbulbs

5G25/PER/822-27/E26/CL/GL/WGD 4/2BC


Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information		Power Factor (Nom)		Temperature	
Base	E26 [Single Contact Medium Screw]		0.7		
Nominal Lifetime (Nom)	15000 h	Voltage (Nom)	120 V		
Switching Cycle	20000X			T-Case Maximum (Nom)	30 °C
Technical Type	5-40W				
Light Technical		Controls and Dimming		Mechanical and Housing	
Color Code	822-827 [tunable warm white]	Dimmable	Yes	Bulb Finish	Clear (CL)
Initial lumen (Nom)	350 lm				
Luminous Flux (Rated) (Nom)	350 lm				
Color Designation	Warm White (WW)	Product Data			
Correlated Color Temperature (Nom)	2200-2700 K	Order product name	5G25/PER/822-27/E26/CL/GL/WGD 4/2BC		
Luminous Efficacy (rated) (Nom)	70.00 lm/W	EAN/UPC - Product	50046677469752		
Color Consistency	<6	Order code	469759		
Color Rendering Index (Nom)	80	Numerator - Quantity Per Pack	1		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Numerator - Packs per outer box	4		
Operating and Electrical		Material Nr. (12NC)	929001315743		
Input Frequency	60 Hz	Net Weight (Piece)	0.040 kg		
Power (Rated) (Nom)	5 W				
Lamp Current (Nom)	45 mA				
Starting Time (Nom)	0.5 s				
Warm Up Time to 60% Light (Nom)	0.5 s				

Classic filament LEDbulbs


Dimensional drawing




Bulb G25 120V 4-40W 350lm2200-2700K E26D

Product	D	C
5G25/PER/822-27/E26/CL/GL/WGD 4/2BC	80 mm	121 mm


Photometric data



LEDBulbs 4-40W E26 G25



LEDBulbs 6-60W E26 G25





General Uniform Lighting

LEDBulbs 4-40W E26 G25

Classic filament LEDbulbs

Lifetime



LEDBulbs 6-60W E26 G25

LEDBulbs 6-60W E26 G25

