



Classic filament LEDbulbs

6G25/AMB/822-827/E26/CL/GL/DIM BC 2PK

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	25,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux	500 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	83.33 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	6 W
Lamp Current (Nom)	60 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	95 °F

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G25 (G25)

Approval and Application	
EyeComfort	Yes


Product Data	
Order product name	6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK
Full product name	6G25/AMB/822-827/E26/CL/GL/DIM BC 2PK

Classic filament LEDbulbs

Order code	469767
Material Nr. (12NC)	929001315803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677469764


Numerator - Packs per outer box	4
EAN/UPC - Case	50046677469769

Dimensional drawing




Product	D	C
6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK	80 mm	121 mm


Photometric data



Spectral Power Distribution Colour - 6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK




Light Distribution Diagram - 6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK




General uniform lighting - 6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK

Classic filament LEDbulbs

Lifetime



Lumen Maintenance Diagram - 6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK



Life Expectancy Diagram - 6G25/AMB/822-27/E26/CL/GL/WGD BC 2PK

