



LED PAR38

12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	12-90W
Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	900 lm
Luminous Intensity (Nom)	4100 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	12 W
Lamp Current (Nom)	112 mA
Wattage Equivalent	90 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	12PAR38/AMB/835/F25/GL/DIM/FB/1PK 6/1
EAN/UPC - Product	046677474690
Order code	474692
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001319604
Net Weight (Piece)	0.385 kg

LED PAR38


Dimensional drawing




PAR38 120V 11-90W 900lm 25D 3500K E26 D

Product	D	C
12PAR38/AMB/835/F25/GL/DIM/FB/1PK 6/1	121 mm	132 mm

Photometric data




General Information 41 Photo Lighting 47 Page 107



LED Classic PAR38 12W E26 835 F25



LED Classic PAR38 12W E26 835 F25



LED Classic PAR38 12-14W E26 835 F25-F40

LED PAR38

Lifetime



LED Classic PAR38 12-14W E26 835 F25-F40

LED Classic PAR38 12-14W E26 835 F25-F40

